
## **Self-drilling screws**

Form M: button head according to DIN ISO 7049 | cross-slot phillips

Steel | zinc-plated | Cr(VI)-free | Thread type ST (sheet metal)

Further information: DIN-standard has been withdrawn







Diameter	Drilling	Sheet	d <sub>k</sub>		d <sub>p</sub>	k		rf	r	Tool
(d)	range starting	metal thickness up to	min.	max.	max.	min.	max.		min.	size
2.9	0.70	1.90	5.30	5.6	2.3	1.95	2.20	5.0	0.4	H1
3.5	0.70	2.25	6.54	6.9	2.8	2.35	2.60	6.0	0.5	H2
4.2	1.75	3.00	7.84	8.2	3.6	2.75	3.05	6.5	0.6	H2
4.8	1.75	4.40	9.14	9.5	4.1	3.25	3.55	8.0	0.7	H2

Length (I)								
nominal size	min.	max.						
9.5	8.75	10.25						
13.0	12.10	13.90						
16.0	15.10	16.90						
19.0	18.00	20.00						
22.0	21.00	23.00						
25.0	24.00	26.00						

Length (I)								
nominal size	min.	max.						
32.0	30.75	33.25						
38.0	36.75	39.25						
45.0	43.75	46.25						
50.0	48.75	51.25						

Diameter	3 ()									
(d)	9.5	13	16	19	22	25	32	38	45	50
2.9	•	•	•							
3.5			•	•		•				
4.2		•	•	•	•	•	•			
4.8										

• Combinations available in the eShop | Other sizes on request