# All technical data refer to the measure mm

# **RIVKLE® HRT Blind rivet nuts**


Aluminium | Flat head | Hexagonal | Hexagonal | Open


Note: Thread according to ISO 6h (ISO 68-1) -Equivalent nut class 8 (compatible screw class 8.8)

Technical information can be found on the last page.




Diameter	Article number	Drilling diameter d		E	L <sub>2</sub>	е		Length (I)	
(d)		nominal size	В	max.		min.	max.	nominal size	S
M 5	23290050501	9	14	1.0	11.0	0.5	3.0	18.1	S = 6.5 - e
M 6	23240060030	9	14	1.5	11.5	0.5	3.0	18.6	S = 6.8 - e
M 8	23240080030	11	17	1.5	15.5	0.5	3.5	23.6	S = 7.0 - e






### **Grip range**

Defines the range of total thickness of the customers part (even if it consists of more than one layer)




## Hole geometry

If round -> diameter If hexagonal -> wigth across flats



Difference of total length before and after installation



\*in accordance to chosen RIVKLE®\*

