All technical data refer to the measure mm

RIVQUICK® Multigrip

Dome head

Note: stainless steel A2 body and stainless steel A2 mandrel

Technical information can be found on the last page.



Diameter	Article number	d ₁	d_2	Drilling diameter d	е	
(d)		nominal size	nominal size	nominal size	min.	max.
3.2	22023132120	3.2	6.5	3.3 - 3.4	1.0	7
4	22023140130	4	8	4.1 - 4.2	2.0	8
4.8	22023148140	4.8	9.5	4.9 - 5.0	1.5	9

Diameter	Diameter Length (I)		Shear	Tensile	
(d)	nominal size	thickness	force (N)	force (N)	
3.2	12	1.1	1700	2200	
4	13	1.5	3800	3400	
4.8	14	1.6	4500	5000	

Symbol list

