All technical data refer to the measure mm

RIVQUICK® Standard rivets

Extra-large head

Note: stainless steel A2 body and stainless steel A2 mandrel

Technical information can be found on the last page.



Diameter	Article number	d ₁	d_2	Drilling diameter d	•	е
(d)		nominal size	nominal size	nominal size	min.	max.
4.8	22133648100	4.8	16	4.9 - 5.0	4.0	6.0
	22133648120				5.5	8.0
	22133648140				7.5	10.0
	22133648160				9.5	12.0
	22133648200				13.5	16.5

Diameter	Length (I)	Head	Shear	Tensile
(d)	nominal size	thickness	force (N)	force (N)
	10		4700	5800
	12			
4.8	14	2		
	16			
	20			

Symbol list

