

# HELICOIL® Plus Kit - Thread repair

G 1/8"-28 - G 1/2"-14 | 1 dimension in 1 length

**Delivery scope:**

- 10 HELICOIL® Plus thread inserts of the same size and length
- HSS HELICOIL® machine tap, straight-fluted
- HELICOIL® manual installation tool
- Practical case for storage and transport
- Operating instructions



Technical information can be found on the last page.

Diameter (d)	Article number	Pitch (P)	D <sub>HC</sub> min.	D <sub>1HC</sub>		Nominal length t <sub>2</sub> (x d)	Nominal length t <sub>2</sub>	W	t <sub>3</sub> max.	B	d <sub>1</sub>	
				min.	max.						min.	max.
G 1/8"-28	41851714004	0.91	10.82	9.91	10.16	1.0	3.2	1.9	2.7	10.00	11.5	12.0
	41851714006					1.5	4.8	3.6	4.3			
	41851714008					2.0	6.4	5.1	5.9			
G 1/4"-19	41851744004	1.34	14.74	13.46	13.72	1.0	6.4	3.1	5.7	13.60	15.7	16.2
	41851744006					1.5	9.5	5.3	8.8			
	41851744008					2.0	12.7	7.4	12.0			
G 3/8"-19	41851774004	1.34	18.25	17.27	17.02	1.0	9.5	5.3	8.8	18.25	19.5	20.0
	41851774006					1.5	14.3	8.5	13.6			
	41851774008					2.0	19.1	11.8	18.4			
G 1/2"-14	41851794004	1.81	23.09	21.59	21.34	1.0	12.7	5.2	11.7	23.09	24.6	25.2
	41851794006					1.5	19.1	8.4	18.1			
	41851794008					2.0	25.4	11.6	24.6			

All technical data refer to the measure mm



## HELICOIL® Plus thread inserts





W and  $d_1$  are the control values for thread inserts (Free Running and Screwlock) before they have been installed. The length can only be measured for installed thread inserts.

### Holding thread



### Assembly



tang not broken off

Prior to tapping, counter-bore 90° and deburr.  
Outside diameter of countersink =  $D_{HC} + 0.1 \text{ mm}$ .

- d = Nominal thread diameter
- P = Thread pitch
- $d_1$  = Outside diameter of thread insert prior to installation
- W = Number of threads prior to installation
- $D_{HC}$  = Outside diameter of the parent thread
- $D_{1HC}$  = Crest diameter
- B = Suitable twist drill diameter. Please note:  $D_{1HC}$  is critical for selecting the correct twist drill diameter.
- $t_1$  = Minimum depth of tapped hole according to DIN 76 – Part 1 (guide value)
- $t_2$  = The nominal length of the thread insert corresponds to the minimum length of the full parent thread for blind holes or the minimum plate thickness for a through hole.
- $t_3$  = Maximum screw-in depth when the tang is not removed
- $t_5$  = Distance of the thread insert from the joint face = 0.25 to 0.5 P, if  $t_2$  corresponds to the above-mentioned minimum value

When you use HELICOIL® Plus thread inserts for volume production, we recommend to add at least  $1 \times P$  to values  $t_1$  and  $t_2$ .

All technical data refer to the measure mm

