

RIVKLE® Standard blind rivet nuts

Stainless steel | Thin head | Knurled | Cylindrical | Closed

Note: RIVKLE® produced in stainless steel for an optimal corrosion resistance | Thread according to ISO 6h (ISO 68-1)

Technical information can be found on the last page.



Diameter (d)	Article number	Drilling diameter d nominal size	B	E max.	L ₂	e		Length (l) nominal size	S
						min.	max.		
M 3	34376030015	5	6.0	0.3	10.2	0.7	1.5	13.0	S = 2.4 - e
	34376030025		6.0	0.3	10.2	1.5	2.5	14.1	S = 3.5 - e
	34376030032		6.0	0.3	10.2	2.0	3.2	14.8	S = 4.6 - e
M 4	34376040030	6	7.0	0.5	12.0	0.7	3.0	15.7	S = 3.8 - e
	34376040035		7.0	0.3	11.9	2.5	3.5	16.7	S = 4.0 - e
	34376040042		7.0	0.3	11.9	2.5	4.2	17.5	S = 4.7 - e
M 5	34376050020	7	8.0	0.3	14.2	0.8	2.0	17.8	S = 3.2 - e
	34376050030		8.0	0.3	14.2	2.0	3.0	18.9	S = 4.3 - e
	34376050045		8.0	0.3	14.2	3.0	4.5	20.5	S = 5.4 - e
M 6	34376060015	9	10.0	0.4	13.7	0.8	1.5	17.3	S = 3.1 - e
	34376060030		10.0	0.4	13.6	1.5	3.0	18.8	S = 4.7 - e
	34376060045		10.0	0.4	13.6	3.0	4.5	20.4	S = 6.3 - e
	34376060060		10.0	0.4	13.6	4.5	6.0	22.0	S = 7.9 - e
M 8	34376080015	11	12.0	0.4	16.7	0.8	1.5	20.3	S = 3.1 - e
	34376080030		12.0	0.4	16.7	1.5	3.0	21.9	S = 4.7 - e
	34376080045		12.0	0.4	16.7	3.0	4.5	23.5	S = 6.3 - e
	34376080060		12.0	0.4	16.7	4.5	6.0	25.1	S = 7.9 - e
M 10	34376100015	13	14.0	0.4	21.9	0.8	1.5	26.3	S = 3.9 - e
	34376100030		14.0	0.4	21.9	1.5	3.0	27.9	S = 5.5 - e
	34376100045		14.0	0.4	21.9	3.0	4.5	29.5	S = 7.1 - e
	34376100060		14.0	0.4	21.9	4.5	6.0	31.1	S = 8.7 - e
M 12	34376120015	16	17.0	0.4	26.2	0.8	1.5	30.5	S = 3.8 - e
	34376120030		17.5	0.4	26.2	1.5	3.0	32.1	S = 3.8 - e
	34376120045		17.5	0.4	26.2	3.0	4.5	33.7	S = 7.0 - e
	34376120060		17.5	0.4	26.2	4.5	6.0	35.3	S = 8.6 - e

All technical data refer to the measure mm





Head diameter
Overall length
Thread size



Grip range
 Defines the range of total thickness of the customers part (even if it consists of more than one layer)



Hole geometry
 If round → diameter
 If hexagonal → width across flats




Head projection after setting
 Variable according to the application (setting load, material substrate, etc.)

Blind side projection after installation
 Defines the clearance needed on the blind side (cannot be used for quality control)

Setting stroke
 Difference of total length before and after installation

RIVKLE® Nut



RIVKLE® Stud



- RIVKLE®
- Mandrel*
- Customers part
- Anvil*
- Counter nut
- Setting tool

in accordance to chosen RIVKLE®

All technical data refer to the measure mm

